







UL/CUL 技术 参数 UL/CUL Technical Data			
等 级 Use Group	B	C	D
额定电压 Rated Voltage [V]	300	—	300
额定电流 Rated Current [A]	15	—	10
接线范围 Wire Range单/多芯线 Solid/Stranded [AWG]	—		
耐电压 Withstanding Voltage	1600V/1Min		
IEC 技术参数 IEC Technical Data			
过电压类别 Overvoltage Category	III	III	II
污染等级 Contamination Class	3	2	2
额定电压 Rated Voltage [V]	250	320	630
额定电流 Rated Current [A]	15	15	15
额定冲击电压 Impulse withstand voltage [KV]	4.0	4.0	4.0
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm²]	—		
一般参数 Other Data			
间距 Pitch /极数 Poles [mm] / [P]	5.08/02-24		
工作温度 Operating temperature [°C]	-40~105		
焊锡温度 Soldering temperature	260°C/5S		
引针尺寸 Pin Dimensions [mm]	1.0*1.0		
PCB板孔径 PCB Hole Diameter [mm]	φ 1.7		
符合RoHS环保要求			

Poles	PART NO.	Dimension mm	
		A	B
2	G-DT508S2P-C000	11.56	5.08
3	G-DT508S3P-C000	16.64	10.16
4	G-DT508S4P-C000	21.72	15.24
5	G-DT508S5P-C000	26.80	20.32
6	G-DT508S6P-C000	31.88	25.40
7	G-DT508S7P-C000	36.96	30.48
8	G-DT508S8P-C000	42.04	35.56
...			
24	G-DT508S24-C000	123.32	116.84

2	Pin	Copper Alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:
CHECKED:	DATE:
DRAWN:	DATE:
YKX	2026-5-22

Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRY CO., LTD			
TITLE: 绿色端子台 DT2EDGVC-5.08-XP 直针 封口			
PART. NO.		G-DT508SXP-C000	
UNIT	mm	SCALE	free
FILE NO.	Ckmtw-DT508-0022	REV.	A WJ00