









71	20.40	21.00	21.63	22.80	21.60
69	19.80	20.40	21.03	22.20	21.00
67	19.20	19.80	20.43	21.60	20.40
65	18.60	19.20	19.83	21.00	19.80
63	18.00	18.60	19.23	20.40	19.20
61	17.40	18.00	18.63	19.80	18.60
59	16.80	17.40	18.03	19.20	18.00
57	16.20	16.80	17.43	18.60	17.40
55	15.60	16.20	16.83	18.00	16.80
53	15.00	15.60	16.23	17.40	16.20
51	14.40	15.00	15.63	16.80	15.60
49	13.80	14.40	15.03	16.20	15.00
47	13.20	13.80	14.43	15.60	14.40
45	12.60	13.20	13.83	15.00	13.80
43	12.00	12.60	13.23	14.40	13.20
41	11.40	12.00	12.63	13.80	12.60
39	10.80	11.40	12.03	13.20	12.00
37	10.20	10.80	11.43	12.60	11.40
35	9.60	10.20	10.83	12.00	10.80
33	9.00	9.60	10.23	11.40	10.20
31	8.40	9.00	9.63	10.80	9.60
29	7.80	8.40	9.03	10.20	9.00
27	7.20	7.80	8.43	9.60	8.40
25	6.60	7.20	7.83	9.00	7.80
23	6.00	6.60	7.23	8.40	7.20
21	5.40	6.00	6.63	7.80	6.60
19	4.80	5.40	6.03	7.20	6.00
17	4.20	4.80	5.43	6.60	5.40
15	3.60	4.20	4.83	6.00	4.80
13	3.00	3.60	4.23	5.40	4.20
11	2.40	3.00	3.63	4.80	3.60
9	1.80	2.40	3.03	4.20	3.00
7	1.20	1.80	2.43	3.60	2.40
No. of Contacts	A	B	C	D	E
Dimension					

- 1.MATERIAL:
1.1 HOUSING: High Temperature Plastic,UL94V-0; COLOR: BLACK.
1.2 ACTUATOR: High Temperature Plastic,UL94V-0; COLOR: BLACK.
1.3 CONTACT: Copper alloy,T=0.10±0.01mm
2.FINISH:
2.1 CONTACT:GOLD PLATING ON CONTACT AREA
GOLD PLATED ON SOLDER TAILS
NICKEL UNDER PLATED OVER ALL



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.X' ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 0.3PH 1.0H 翻盖下接FPC
UNIT: mm [inch]	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW5C-03FPCXX-100B
SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2604271037
			SHEET NO. 1 OF 1