

SLIDE SWITCH

碩方精密電子開關

www.Sofng.com

Operation: SMT/贴片卧式 中小型 滑动开关 [柄长/操作力可定制]



LTEM NO.: MS-214H-** (Series)

(L13.0mm × W3.50mm SLIDE-SWITCH)

表面贴装 SMT

側向操作 LATERAL

精密部品 NICETY

可靠 STABILIZE


適合環保 RoHS

Technical parameter

PROJECT	LEVEL	A[better product]	B[average product]
Electrical	Contact Rating	0.3A, 30V DC	
	Initial Contact Resistance	50mΩ max.	
Properties	Insulation Resistance	100MΩ min.500V DC Skey/PD: 100MΩ min.300V DC	
	Withstand Voltage	300V AC for 1 minute	250 V AC for 1 minute
Durable Performance	There No Load	15,000 Cycles	10,000 Cycles
	Rated Load	12,000 Cycles	8,500 Cycles
	Storage temp.	-25℃~+75℃(Operating Temp:)	
	Operating Force	2. 6N. (1N.=100gram-force)	
	Heat Rrsistance	IR Reflow:255℃, 5sec. Manual:350℃, 3sec.	

Material declaration		
No.	NAME	Description
① A	拨柄	PA6T (Black)耐高温尼龙
② B	盖板	不锈钢 SUS304 t=0.4mm
③ C	基座	PA6T (Black)耐高温尼龙
④ D	簧片	磷铜 C5210 G/F
⑤ E	嵌件	黄铜 C2680(Qsn6.5-01 镀银) t=0.30

CIRCUIT DIAGRAM



Unit:mm

P.C.B LAYOUT

