




SPECIFICATIONS

Current Rating: 3Amps

Insulation Resistance: 1000MΩ Min

Contact Resistance: 20mΩ Max

Withstanding Voltage: AC 1000V




Operation Temperature: -40°to+105°

Contact Material: Brass

Standard: PA6T

Insulator Material: Polyester(UL 94V-0)

Contact Plating: Gold Flash

Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
PM2.54-YD2S-01A	1	0.00	2.54
PM2.54-YD2S-02A	2	2.54	5.08
PM2.54-YD2S-03A	3	5.08	7.62
PM2.54-YD2S-04A	4	7.62	10.16
PM2.54-YD2S-05A	5	10.16	12.70
PM2.54-YD2S-06A	6	12.70	15.24
PM2.54-YD2S-07A	7	15.24	17.78
PM2.54-YD2S-08A	8	17.78	20.32
PM2.54-YD2S-09A	9	20.32	22.86
.....			
PM2.54-YD2S-40A	40	(PIN-1)X2.54	(PIN)X2.54

DIMENSION IN mm

TOLERANCE UNLESS
OTHERWISE SPECIFIED

.X±0.50

X.*± 5°

.XX±0.20

.X.*± 3°

.XXX±0.10

.XX.*± 1°

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd

APR.

Alex

CHK.

Jack

DRA.

Can

TITLE:

2.54FH H8.5 2xPin 90度 Y型 PC3.2 PB12.7 6T

DWG NO.

PM2.54-YD2S-NA

PROJ.

CUSTOMER DRAWING

SIZE A4

SCALE 1:1

SHEET 1/3

REV. A