


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		L	REVISED PER ECO-14-011808	09AUG2014	AP	SB

D


C

B



A



- CONNECTOR ACCEPTS SIZE 20 DF PIN CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
- CONNECTOR COMPLIES WITH 108-40005 WHERE APPLICABLE.
- MOLDED PARTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK
- SHELLS: STEEL PER ASTM A109.
- ZINC PLATED PER ASTM B633; TYPE II; CLASS SC1; YELLOW CHROMATE.
- TIN OR TIN-LEAD PLATED OVER COPPER UNDERPLATE.
- CHROME PLATED.
- TIN PLATED OVER COPPER UNDERPLATE.
- ZINC PLATED .000200-.000400 THICK, YELLOW TRIVALENT CHROMIUM CHROMATE COATING.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



10	OBSOLETE	SMALL PACK	9	NO	1-205204-0
		STANDARD	9	NO	205204-9
		STANDARD	8	NO	205204-8
SUPERSEDED BY 205204-9		SMALL PACK	5	NO	205204-7
		STANDARD	8	YES	205204-4
SUPERSEDED BY 205204-8		STANDARD	6	NO	205204-3
OBSOLETE		STANDARD	7	NO	205204-2
SUPERSEDED BY 205204-9		STANDARD	5	NO	205204-1
PACKAGING TYPE			SHELL FINISH	GROUNDING INDENTS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 07/19/85	 TE Connectivity							
DIMENSIONS: INCHES		CHK J. GERACE 07/29/85								
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	NAME PLUG CONNECTOR, SIZE 1, 9 POS., AMPLIMITE HDP —						
	0 PLC ± —		PRODUCT SPEC —							
	1 PLC ± —		—							
	2 PLC ± —		APPLICATION SPEC —							
	3 PLC ± .005		—							
	4 PLC ± —		—	SIZE A2	CAGE CODE 00779	DRAWING NO C-205204	RESTRICTED TO —			
	ANGLES ± ±		WEIGHT —							
MATERIAL SEE NOTES		FINISH SHELLS: SEE TABLE	CUSTOMER DRAWING					SCALE NTS	SHEET 1 of 1	REV L

D

C

B

A

205204