

REVISIONS

规格:

- Materiali:

材料:

- PART NO.:

X02 37 W T 7 W 5
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series NO.
②Row No.Pin No.XX-09;15;25;37
③Welding Board Angle :W-Male
④T: Traditional C: Car-pin
⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U'
⑥Color:B-BLACK W-White BL-Blue
⑦1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7

NUMBER OF POSITIONS	DIMENSION			
	A $\pm$ 0.25	B $\pm$ 0.13	C $\pm$ 0.38	D $\pm$ 0.25
9	30.80	24.99	18.00	19.28
15	39.20	33.32	26.50	27.51
25	53.05	47.04	40.00	41.28
37	69.40	63.50	56.60	57.71

铆合方式	TYPE-1: 铆合	TYPE-2: 前铆实心螺母	TYPE-7: 后铆鱼叉	TYPE-5: 铆鱼叉锁螺丝
图示				

DESIGN	阿树	VIEW:		MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in		PART NO.: X0237WT7W5
APPROVED		SIZE: A4		DWG NO.: X-X0237WT7W5
PRECISION CO., LIMITED			SCALE N/A	PAGE 1/1
				REVISION A1

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	

XKLB 星城
Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

www.helloxkb.com	www.helloxkb.cn	www.xk-dq.cn
------------------	-----------------	--------------

XKB INDUSTRIAL PRECISION CO.,LIMITED