






ROHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

Part No	CKT	A	B	C	D	E
BTB0.544-10PLBDC2-MB42	2X5	2.00	3.20	4.70	6.06	4.10
BTB0.544-12PLBDC2-MB42	2X6	2.50	3.70	5.20	6.56	4.60
BTB0.544-14PLBDC2-MB42	2X7	3.00	4.20	5.70	7.06	5.10
BTB0.544-16PLBDC2-MB42	2X8	3.50	4.70	6.20	7.56	5.60
BTB0.544-18PLBDC2-MB42	2X9	4.00	5.20	6.70	8.06	6.10
BTB0.544-20PLBDC2-MB42	2X10	4.50	5.70	7.20	8.56	6.60
BTB0.544-22PLBDC2-MB42	2X11	5.00	6.20	7.70	9.06	7.10
BTB0.544-24PLBDC2-MB42	2X12	5.50	6.70	8.20	9.56	7.60
BTB0.544-26PLBDC2-MB42	2X13	6.00	7.20	8.70	10.06	8.10
BTB0.544-28PLBDC2-MB42	2X14	6.50	7.70	9.20	10.56	8.60
BTB0.544-30PLBDC2-MB42	2X15	7.00	8.20	9.70	11.06	9.10
BTB0.544-32PLBDC2-MB42	2X16	7.50	8.70	10.20	11.56	9.60
BTB0.544-34PLBDC2-MB42	2X17	8.00	9.20	10.70	12.06	10.10
BTB0.544-36PLBDC2-MB42	2X18	8.50	9.70	11.20	12.56	10.60
BTB0.544-38PLBDC2-MB42	2X19	9.00	10.20	11.70	13.06	11.10
BTB0.544-40PLBDC2-MB42	2X20	9.50	10.70	12.20	13.56	11.60
BTB0.544-44PLBDC2-MB42	2X22	10.50	11.70	13.20	14.56	12.60
BTB0.544-50PLBDC2-MB42	2X25	12.00	13.20	14.70	16.06	14.10
BTB0.544-60PLBDC2-MB42	2X30	14.50	15.70	17.20	18.56	16.60
BTB0.544-70PLBDC2-MB42	2X35	17.00	18.20	19.70	21.06	19.10
BTB0.544-80PLBDC2-MB42	2X40	19.50	20.70	22.20	23.56	21.60

MANUFACTURE DWG

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: X.: ±0.50 X.X: ±0.20 X.XX: ±0.10

ANGLES: ±1°

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co., Ltd

TITLE: 0.5 Pitch B型单槽立式BTB母座业务图(单高4.4)

PAR BTB0.544-XPLBDC2-MB42

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE 1:1 UNIT: MM

SIZE: A4

SHEET: 1F1

REV: A

MAPX	MODIFICATION	DATE	DRAW	APPROVE
序号	品名	材质		
①	0.5 Pitch B型单槽立式BTB母座胶芯	LCP UL94 V-0 颜色:米黄色		
②	0.5 Pitch B型单槽立式BTB母座端子	铜合金/表面点镀金		
③	0.5 Pitch B型单槽立式BTB母座焊片	铜合金/表面镀锡		