






Features :

- T-568A/B Dual wiring
- RJ45 complies with FCC part 68 standard
- Provides termination for 22~26 AWG wire
- Jack insertion life >750 mating cycles
- Operating temperature : -40°C~+60°C

Electrical :

- Contact resistance : 20m ohm
- DC Current rating : 1.5Amps
- DC resistance : Max.0.1 ohm
- Insulation Resistance : 500m ohm
- Dielectric withstanding voltage : 1000V

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

MATERIAL	
CATEGORY	■ CAT.5E ■ CAT.6 ■ CAT.6A ■ CAT.7 □ CAT.8
HOUSING	ABS+PC UL94V-0
CONTACT	0.35mm THICKNESS PHOSPHOR BRONZE GOLD PLATED OVER NICKEL
GOLD-PLATING	☐ 0.0762um/3u inch ☐ 0.15um/6u inch ☐ 0.38um/15u inch ☐ 0.76um/30u inch ☐ 1.27um/50u inch
COLOR	☐ WHITE ☐ BLACK ☐ GREEN ☐ BLUE ☐ YELLOW ☐ RED ☐ ORANGE ☐ IVORY ☐ OTHER _____
TYPE OF PRODUCT	☐ UNSHIELD ■ SHIELD : ZINC ALLOY, NICKLE PLATED.

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: RJ45 CAT.7 屏蔽直通连接头			
DRAWN: LYF	DATE: 2024-05-07	PART. NO.		R-RJ45Z08P-B003	
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0485	REV.	A ZJDZ