




H
G
F
E
D
C
B
A



REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

NOTE 1:
UL标准 (UL Standard)
1. 额定电压与电流: 300V/10A
Rated voltage/Rated current: 300V/10A
2. 功频耐压: AC1600V/Min
Withstanding Voltage: AC2000V/Min
3. 线径范围: 30~12AWG
Wire range: 30~12AWG
IEC标准 (IEC Standard)
1. 额定电压与电流: 250V/18A
Rated voltage/Rated current: 250V/18A
2. 线径范围: 2.5mm²
Wire range: 2.5mm²
NOTE 2:
1. 间距 (Pitch): 5.08mm
2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
3. 剥线长度: 6~7mm
Stripping length: 6~7mm
4. 符合RoSH环保要求
RoHS Compliance
5. 额定扭矩: 0.4N.m 3.54[Lb. in]
(Rated torque): 0.4N.m 3.54[Lb. in]
6. 未标注公差表
Undimensioned tolerances

2级方向公差 (mm)				其他尺寸公差 (mm)				公差带	
Pitch range in mm				Nominal dimension range in mm				Tolerance zone	
≤6	6~10	10~24	≥30	30~60	60~100	100~150	>150	0.1/10	∠
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70	±1.00	±1'	

订购方式 (HOW TO ORDER)
MX128G- 5.08-□□□□-□-□□□□
型号 间距 极数 客户型号
Series NO. Pitch Poles Customer Request
颜色 (Color)
1. 单间距 Single Pitch
2. 双间距 Double Pitch
1. 灰色 (Gray) 2. 蓝色 (Blue)
3. 黑色 (Black) 4. 绿色 (Green)
5. 橙色 (Orange) 6. 红色 (Red)
7. 黄色 (Yellow) 8. 白色 (White)
9. 透明 (Transparent)

4	(Cage)方盒	(Copper alloy) 铜合金	(Ni plated)镀镍	PART NO.: /
3	(Contact)触点	(Copper alloy) 铜合金	(Sn plated)镀锡	APPD: /
2	(Screw)螺丝 M3	(Steel) 钢	(Ni plated)镀镍	CHKD: /
1	(Housing)塑件	PA66	UL94V-0	DRFT: /
ITEM	NAME OF PART	MATERIAL	NOTES	 THIED ANGLE PROJECTION

 安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD			
型号	MX128G-5.08-XXP-1X-XXAH		
系列	MX128G-5.08	页码	1/1
图号	MX128G508001	比例	1:1

8 7 6 5 4 3 2 1

8 7 6 5 4 3 2 1