

Rohs

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance: 20m Ω Max

Withstand Voltage:400V AC/DC

Insulation Resistance: 800M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30–60 seconds

(260°C for 10 seconds)



Ordering Information

XXXXX X XX X XXXX

产品类型	间距	总Pin数
J=筒牛	1=1.27	016=16P

产品形态
1=DIP

00=常规

塑膠材料
1=PBT

1=黑色

包裝方式
1=管裝

序列号
0001-9999

$$A = 1.27 \times 2.54$$

Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001		2.8		5.65	5.5
002					

深圳市连盛精密连接器有限公司									
PART NO.		1030200146							
TITLE:		2.0Box Npin H5.65 180°							
PROJ.									
SCALE		FIT							
UNIT		mm							
SIZE		A4							
SHEET		1/1							
REV	DATE	MODIFICATION		DESCRIPTION		CHANGE			
A0	2012.03.28	NEW DRAWING							
OPERATION		DRAW							
X.X		±0.30							
X.XX		±0.20		CHECK					
X.XXX		±0.10							
Angle		±3°		APPROVE					
DIM		TOL							