



说明:

1. 特性:

额定电压 : 500V AC MIN

小针额定电流 : 5A

大针额定电流 : 10A, 20A, 30A, 40A

接触阻抗 : $30\text{m}\Omega$ MAX.

绝缘阻抗 : $3000\text{M}\Omega$ MIN. at 500V DC

耐电压值 : 1000V AC RMS for 1Minute

温度范围 : -55°C ~ $+105^{\circ}\text{C}$

盐雾时间 : 48H

2. 材料:

胶芯 : PBT, rated UL94V-0

接触点: 铜合金, 镀金 $1\mu\text{''}$ ~ $30\mu\text{''}$

铁壳 : SPCC, 前壳镀镍后壳镀锡

额定电流	ϕA	ϕB	适用线径
10A	$\phi 2.60$	$\phi 1.80$	14~16AWG
20A	$\phi 3.60$	$\phi 2.80$	10~12AWG
30A	$\phi 4.50$	$\phi 3.50$	8~10AWG
40A	$\phi 5.40$	$\phi 4.60$	6~8AWG

TOLERANCE TABLE	
.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: DW-21W4M 公头 焊线式 长针 全金 光孔			
DRAWN: LYF	DATE: 2024-01-13	PART. NO.	D-DW021WPM-A000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DW-00049	REV.	A QT00