

ROHS Compliant

A

B

C

D

E






F

G

H

I

J



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

Part No	CKT	A	B	C	D	E
BTB0.526-10PLBDC2-GB42	2X5	2.00	3.10	4.60	5.52	4.10
BTB0.526-12PLBDC2-GB42	2X6	2.50	3.60	5.10	6.02	4.60
BTB0.526-14PLBDC2-GB42	2X7	3.00	4.10	5.60	6.52	5.10
BTB0.526-16PLBDC2-GB42	2X8	3.50	4.60	6.10	7.02	5.60
BTB0.526-18PLBDC2-GB42	2X9	4.00	5.10	6.60	7.52	6.10
BTB0.526-20PLBDC2-GB42	2X10	4.50	5.60	7.10	8.02	6.60
BTB0.526-22PLBDC2-GB42	2X11	5.00	6.10	7.60	8.52	7.10
BTB0.526-24PLBDC2-GB42	2X12	5.50	6.60	8.10	9.02	7.60
BTB0.526-26PLBDC2-GB42	2X13	6.00	7.10	8.60	9.52	8.10
BTB0.526-28PLBDC2-GB42	2X14	6.50	7.60	9.10	10.02	8.60
BTB0.526-30PLBDC2-GB42	2X15	7.00	8.10	9.60	10.52	9.10
BTB0.526-32PLBDC2-GB42	2X16	7.50	8.60	10.10	11.02	9.60
BTB0.526-34PLBDC2-GB42	2X17	8.00	9.10	10.60	11.52	10.10
BTB0.526-36PLBDC2-GB42	2X18	8.50	9.60	11.10	12.02	10.60
BTB0.526-38PLBDC2-GB42	2X19	9.00	10.10	11.60	12.52	11.10
BTB0.526-40PLBDC2-GB42	2X20	9.50	10.60	12.10	13.02	11.60
BTB0.526-44PLBDC2-GB42	2X22	10.50	11.60	13.10	14.02	12.60
BTB0.526-50PLBDC2-GB42	2X25	12.00	13.10	14.60	15.52	14.10
BTB0.526-60PLBDC2-GB42	2X30	14.50	15.60	17.10	18.02	16.60
BTB0.526-70PLBDC2-GB42	2X35	17.00	18.10	19.60	20.52	19.10
BTB0.526-80PLBDC2-GB42	2X40	19.50	20.60	22.10	23.02	21.60

MANUFACTURE DWG

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS:

X.:±0.50

X.X:±0.20

X.XX:±0.10

ANGLES:

±1°



东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,Ltd



TITLE:0.5 Pitch B型单槽立式BTB公座业务图(单高2.6)

PAR BTB0.526-XPLBDC2-GB42

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE:1:1 UNIT:MM

CUSTOMER COPY

SIZE:A4 SHEET:1F1 REV:A

A

B

C

D

E

F

G

H

I

J