


H
G
F
E
D
C
B
A

8 7 6 5 4 3 2 1

REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE



- NOTE 1:
- UL标准 (UL Standard)
- 额定电压与电流: 300V/10A
Rated voltage/Rated current: 300V/10A
 - 功频耐压: AC1600V/Min
Withstanding Voltage: AC2500V/Min
 - 线径范围: 30~12AWG
Wire range: 30~12AWG
- IEC标准 (IEC Standard)
- 额定电压与电流: 450V/18A
Rated voltage/Rated current: 450V/18A
 - 线径范围: 2.5mm²
Wire range: 2.5mm²
- NOTE 2:
- 间距 (Pitch): 7.50mm
 - 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
 - 剥线长度: 6~7mm
Stripping length: 6~7mm
 - 符合RoHS环保要求
RoHS Compliance
 - 额定扭矩: 0.4N.m 3.54[Lb. in]
(Rated torque): 0.4N.m 3.54[Lb. in]
 - 未标注公差表
Undimensioned tolerances

Pitch range in mm			Nominal dimension range in mm					
≤6	6~10	10~24	≤30	30~60	60~100	100~150	>150	0.1/10 <
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70	±1.00	±1°

订购方式 (HOW TO ORDER)

MX128V - 7.50 - □□P - □ - □□□□

型号 间距 极数 客户型号
Series NO. Pitch Poles Customer Request

颜色 (Color)

- 单间距 Single Pitch
- 双间距 Double Pitch
- 灰色 (Gray)
- 蓝色 (Blue)
- 黑色 (Black)
- 绿色 (Green)
- 橙色 (Orange)
- 红色 (Red)
- 黄色 (Yellow)
- 白色 (White)
- 透明 (Transparent)

4	(Cage)方盒	(Copper alloy) 铜合金	(Ni plated)镀镍	PART NO.: /	安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD				
3	(Contact)触点	(Copper alloy) 铜合金	(Sn plated)镀锡	APPD: /					
2	(Screw)螺丝 M3	(Steel)钢	(Ni plated)镀镍	CHKD: /	型号	MX128V-7.50-XXP-1X-XXAH			
1	(Housing)塑件	PA66	UL94V-0	DRFT: /					
ITEM	NAME OF PART	MATERIAL	NOTES	 THIED ANGLE PROJECTION	系列	MX128V-7.50	页码	1/1	
					图号	MX128750001	比例	1:1	

8 7 6 5 4 3 2 1