



东莞市讯普电子科技有限公司  
Dongguan Xunpu Electronic Technology Co.,

## 承 认 书

### SPECIFICATION FOR APPROVAL

客 户 名 称 Customer: \_\_\_\_\_

贵司料号CUSTOMER P/N: \_\_\_\_\_

FFC cable 0.5mm,27P,total length 100mm,reverse,gold finger 4mm,reinforcing plate 8mm

敝司料号INTERIOR P/N: \_\_\_\_\_ FFC-0.5-27-100-B-4-8

#### 贵公司承认印 Approval signatures





| 料 号/Part No. | 签 章/Signatures |
|--------------|----------------|
|              |                |

Send us a copy of reference, thank you!

日期 Date:

|             |    |
|-------------|----|
| 拟制/Drawn    | 李晴 |
| 审核/Check    | 陈军 |
| 批准/Approved | 陈钰 |





#### Precautions

1. The body image is for relationship comparison only, and everything is subject to the specifications of the data sheet.

#### Structure

| NO. | Project           | Specification |        | Remark  |
|-----|-------------------|---------------|--------|---------|
| 1   | Insulating film   | Print 20624   | 43um   | 60V 80C |
|     |                   | Blank film    | 43um   |         |
| 2   | Stiffeners        | Blue          | 225um  | PET     |
| 3   | Conductor tinning | Thickness     | 0.035  | ±0.005  |
|     |                   | Width         | 0.3    | ±0.03   |
| 4   | Conductor plating | Electroplate  | Tin Sn | ≥40u"   |
|     |                   | Electroplate  |        |         |

#### Size

|                                                |       |      |       |
|------------------------------------------------|-------|------|-------|
| Number of conductor cores                      | N     | 27   |       |
| Spacing                                        | P     | 0.5  | ±0.05 |
| Total spacing                                  | Pt    | 13   | ±0.08 |
| Overall width                                  | W     | 14   | ±0.08 |
| Edge width                                     | M     | 0.5  | ±0.08 |
| Overall length                                 | L     | 100  | ±1.5  |
| Mating thickness                               | T1    | 0.3  | ±0.05 |
| Thickness of the thread                        | T2    | 0.12 | ±0.03 |
| The inclination of the line mouth              | A     |      | ≤0.3  |
| Punching inclination                           | B     |      | ≤0.5  |
| The length of the bare copper at the wire port | S1/S2 | 4/4  | ±0.05 |
| Length of stiffener                            | B1/B2 | 8/8  | ±1    |

#### Ancillary checklists

| NO. | Project | Specification | Quantity |
|-----|---------|---------------|----------|
| 1   |         |               |          |
| 2   |         |               |          |
| 3   |         |               |          |

1. Shelf life: 12 months for gold plating; Tin plating for 6 months.

2. Storage environment: temperature 0°C~38°C; Humidity 20%~70%RH.

#### Specifications and models:

FFC-0.5-27-100-B-4-8

Customer part number:

Customer model:



东莞市讯普电子科技有限公司

|         |                   |            |             |                    |                |                |           |          |
|---------|-------------------|------------|-------------|--------------------|----------------|----------------|-----------|----------|
| Version | Content of change | date       | Name:       | FFC flexible cable | Figure number: | XP2024080501   | Drawing:  | Li ming  |
| A/O     | New production    | 2022/09/05 | Proportion: | FIT                | Unit:          | Millimetre(mm) | Audit:    | Chen Jun |
|         |                   |            | Vision:     |                    | Page number:   | Page 1 of 1    | Approved: | Xiang Yu |