








3D VIEW



SCHEMATIC

P.C.B LAYOUT
TOP VIEW

(ø3.50mm 4 POLE PLUG DETAIL DRAWING)

NOTES:

1. CONTACT CURRENT RATING:1A;
2. CONTACT RESISTANCE:50mΩ MAX;
3. INSULATION RESISTANCE:100MΩ MIN;
4. DIELECTRIC WITHSTANDING:500V AC MIN;
5. DURABILITY:5000CYCLES MIN;
6. CONNECTOR MATING FORCES:2.94~29.4N(0.3~3.0kgf);
7. CONNECTOR UNMATING FORCES:2.94~29.4N(0.3~3.0kgf);

ITEM	PART NAME	Q'TY	MATERIAL	DESCRIPTION
06	HOUSING	1 PCS	HIGH TEMPERATURE PLASTIC	BLACK,
05	CONTACT E	1 PCS	STAINLESS STEEL, T=0.20	Matte Tin
04	CONTACT C	1 PCS	PHOSPHOR BRONZE, T=0.20	Matte Tin
03	CONTACT B	1 PCS	PHOSPHOR BRONZE, T=0.20	Matte Tin
02	CONTACT B	1 PCS	PHOSPHOR BRONZE, T=0.20	Matte Tin
01	CONTACT A	1 PCS	PHOSPHOR BRONZE, T=0.20	Matte Tin




深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30
X.XX ±0.25
X.XXX ±0.15

X' ±2" X.X' ±0.5'



UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

PJ-327F 插件

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW02-PJ327F-140B

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2609211140

SHEET NO.

1 OF 1