





PCB LAYOUT
(TOP VIEW)



General Specification
Current Rating: 1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment: -20℃~+70℃
Standard Temperature: -40℃~+85℃
Industrial Temperature: -40℃~+85℃
Humidity: 20~70%
Contact Resistance: $\leq 30m\Omega$
Insulation Resistance: $\geq 500M\Omega$
Dielectric Strength: 500V AC/(50HZ)/Min
Mating And Unmating Force: 3~20N
Durability: 750 Cycles Min

Material Specification
Housing : Thermo-plastic, UL94V-0.
Contact : Alloy Copper
Shield : Alloy Copper
Please refer to the customer drawing when customer has specified

网络插座外形图



温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

序号	名称	材料	数量	镀层/颜色	备注
1	插座	PA9T	1	GREY	
2	插针	PHOSPHOR BRONZE	4	RJ45	

图: 吴素飞 日期: 202304026

品名: RCH-5311-12 TH 灰座

审核: 日期:

料号: 531112TKH-20000010TJ10 (WR50001)

审核: 日期:

型号: RJ45 图号:

核准: 日期:

角度: $\pm 2^\circ$ 版本: 1 of 1 单位: mm 比例: 1:1 纸张: A4

1

2

3

该

图

面

供

温

州

瑞

川

电

子

有

限

公

司

内

部

使

用

不

得

私

自

复

印