




- Specifications:
- 1. Rated Voltage : 125V AC/DC
 - 2. Rated Current : 1A AC,DC
 - 3. Withstand Voltage : 200V AC/minute
 - 4. Contact Resistance : 50mΩ (MAX.)
 - 5. Insulation Resistance : 100MΩ (MIN.)
 - 6. Storage Temperature Range: -40℃~+85℃;
 - 7. Operation Temperature Range: -25℃~+70℃;

PIN数	A±0.15	B±0.15	C±0.15
2P	7.60	4.50	1.25
3P	8.85	5.75	2.50
4P	10.10	7.00	3.75
5P	11.35	8.25	5.00
6P	12.60	9.50	6.25
7P	13.85	10.75	7.50
8P	15.10	12.00	8.75
9P	16.35	13.25	10.00
10P	17.60	14.50	11.25
11P	18.85	15.75	12.50
12P	20.10	17.00	13.75
13P	21.35	18.25	15.00
14P	22.60	19.50	16.25
15P	23.85	20.75	17.50
16P	25.10	22.00	18.75

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注
	品名 TITLE	针座		
	料号 PART NO	HCZZ0015G-4		
一般公差 TOLERANCE		比例 SCALE	1:1	
X. xxx ±0.05 X. xx ±0.15 X. x ±0.25		单位 UNIT	MM	制图 DRAW
ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°		张数 PART NO	1 OF 1	审核 CHECKED
		版本 REV	A	夏操云
				批准 APPROVE
				赵亮亮

