





REV.	DESCRIPTION	DATE



N01 ES:

1. Rated voltage: 250VAC,DC.
2. Rated current: 3A AC,DC.
3. Contact resistance: ≤20 mΩ
4. Insulation resistage: ≥1000 MΩ
5. Withstand voltage: ≥800V AC/minute.
6. Ambient temperature: -25℃~85℃.
7. Materials:NYLON 66 UL94V-0(2).
8. Green Material RoHS Compliant.

孔位	A	B	C
2孔	2.5	7.0	5.4
3孔	5	9.5	7.9
4孔	7.5	12.0	10.4
5孔	10	14.5	12.9
6孔	12.5	17	15.4
7孔	15	19.5	17.9
8孔	17.5	22.0	20.4
9孔	20	24.5	22.9
10孔	22.5	27.0	25.4
11孔	25	29.5	27.9
12孔	27.5	32.0	30.4
13孔	30	34.5	32.9
14孔	32.5	37	35.4
15孔	35	39.5	37.9
16孔	37.5	42	40.4

.X: ±0.25 X°: ±9.0°				DRAWN BY	浙江深海电子有限公司	
.XX: ±0.15 X°: ±2.0°				CHK. BY		
.XXX: ±0.01 XX°: ±1.0°				APRV. BY		
UNIT	SIZE	SCALE		DRAWING NO.	SHEET	PROD. NAME
MM	A4	1:1			1 OF 1	PART NO.
					TITLE	