







MAPX	MODIFICATION	DATE	DRAW	APPROVE
序号	品名	材质		
①	0.5 Pitch D型 单槽侧插BTB公座胶芯	LCP UL94 V-0,颜色:本色		
②	0.5 Pitch D型 单槽侧插BTB公座端子	铜合金/表面点镀金		



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



Part No	CKT	A	B	C	D
BTB0.533-4PWZDB4-GB42	2*2	0.50	2.50	2.50	1.70
BTB0.533-6PWZDB4-GB42	2*3	1.00	3.00	3.00	2.20
BTB0.533-8PWZDB4-GB42	2*4	1.50	3.50	3.50	2.70
BTB0.533-10PWZDB4-GB42	2*5	2.00	4.00	4.00	3.20
BTB0.533-12PWZDB4-GB42	2*6	2.50	4.50	4.50	3.70
BTB0.533-14PWZDB4-GB42	2*7	3.00	5.00	5.00	4.20
BTB0.533-16PWZDB4-GB42	2*8	3.50	5.50	5.50	4.70
BTB0.533-18PWZDB4-GB42	2*9	4.00	6.00	6.00	5.20
BTB0.533-20PWZDB4-GB42	2*10	4.50	6.50	6.50	5.70
BTB0.533-22PWZDB4-GB42	2*11	5.00	7.00	7.00	6.20
BTB0.533-24PWZDB4-GB42	2*12	5.50	7.50	7.50	6.70
BTB0.533-26PWZDB4-GB42	2*13	6.00	8.00	8.00	7.20
BTB0.533-28PWZDB4-GB42	2*14	6.50	8.50	8.50	7.70
BTB0.533-30PWZDB4-GB42	2*15	7.00	9.00	9.00	8.20
BTB0.533-32PWZDB4-GB42	2*16	7.50	9.50	9.50	8.70
BTB0.533-34PWZDB4-GB42	2*17	8.00	10.00	10.00	9.20
BTB0.533-36PWZDB4-GB42	2*18	8.50	10.50	10.50	9.70
BTB0.533-38PWZDB4-GB42	2*19	9.00	11.00	11.00	10.20
BTB0.533-40PWZDB4-GB42	2*20	9.50	11.50	11.50	10.70
.....	...	...	...	...	...
BTB0.533-80PWZDB4-GB42	2*40	19.50	21.50	21.50	20.70
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES				TITLE: 0.5 Pitch D型单槽侧插BTB公座业务图(单高3.3)	
DECIMALS:		PAR		BTB0.533-XPWZDB4-GB42	
X.: ±0.50		DWN		Lucas	
X.X: ±0.20		CHKD		Ethan	
X.XX: ±0.10		APVD		Jacob	
		SCALE: 1:1		UNIT: MM	
		CUSTOMER COPY		SIZE: A4	
				SHEET: 1F1	
				REV: A	