






MATED CONDITION



With Mylar



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05



With Cover

NOTES:

1. MATERIAL:

1.1 HOUSING: THERMOPLASTIC, HIGH TEMP.,
UL94V-0;

1.2 CONTACT: COPPER ALLOY

1.3 FITTING NAIL: COPPER ALLOY

2. FINISH:

2.1 CONTACT:

PER ACES P/N PLATING CODE.

2.2 FITTING NAIL:

PER ACES P/N PLATING CODE.

3. REFLOW SOLDER CAPABLE TO 260°C

PER ACES SPEC.

BTB 7 5 3 0 - * * * S - B 0 R

PACKING: R:REEL

0:WITH POSITIONING POSTS

1:WITHOUT POSITIONING POSTS

COLOR:BLACK

S: SOCKET

PIN

PLATING: G:GOLD FLASH

HEIGHT30--3.0H

5:0.50 BTB

BTB CONNECTOR SERIES

CKT	A	B	C
16	3.50	5.50	8.50
20	4.50	6.50	9.50
30	7.00	9.00	12.00
40	9.50	11.50	14.50
50	12.00	14.00	17.00
60	14.50	16.50	19.50
70	17.00	19.00	22.00
80	19.50	21.50	24.50
100	24.50	26.50	29.50
120	29.50	31.50	34.50

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO., LTD			
CHECKED:	DATE:	TITLE: BTB0. 5-30P 单槽母座 塑高3.0 立贴 (合高7.0mm)			
DRAWN: YKX	DATE: 2026-6-26	PART. NO.		Z-BTB0530P-F700	
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-BTB-B009	REV.	A LXW0

TOLERANCE TABLE	
. 0	± 0.30
. 00	± 0.20
. 000	± 0.05