

HSF



ROHS

SPECIFICATIONS

- Voltage rating: 250V AC,DC
- Current rating: 3A AC,DC
- Withstanding Voltage: 1000V AC/minute
- Insulation resistance:1000M Ω min
- Temperature range: -40°C~+105°C


WAFER

- Part NO: AW2505V-xP
- Material: Pin: Brass/Tin over Nickel
Insulator: Nylon 66, UL94V-0
- Mates with: AH2505 series Housing
- Color: Beige

Ordering Information & Dimensions

PART NO.	Dimensions	
	AB	
5264 -2P	2.50	7.50
5264 -3P	5.00	10.00
5264 -4P	7.50	12.50
5264 -5P	10.00	15.00
5264 -6P	12.50	17.50
5264 -7P	15.00	20.00
5264 -8P	17.50	22.50
5264 -9P	20.00	25.00
5264 -10P	22.50	27.50
5264 -11P	25.00	30.00
5264 -12P	27.50	32.50
5264 -13P	30.00	35.00
5264 -14P	32.50	37.50
5264 -15P	35.00	40.00
5264 -16P	37.50	42.50
5264 -17P	40.00	45.00
5264 -18P	42.50	47.50
5264 -19P	45.00	50.00
5264 -20P	47.50	52.50

Unit: m




Unless Otherwise specified tolerance
X. ± 0.35 X.XX: ± 0.20
X.X: ± 0.25 X.XXX: ± 0.15

SCALE: As Shown UNIT: mm

DRAW Jack Bao DATE 5/2/2018

CHECK Bob Yang DATE 5/2/2018



3rd ANGLE PROJECTION



ANTENK ELECTRONICS CO.,LTD
Http://www.antenk.com
E-mail:sales@antenk.com

TITLE: 2.50mm pitch 180° Wafer Connector Series

DRAWING NO: **5264-2A**

PRODUCT NO: **5264-2A**

REV DESCRIPTION

DATE