






UL/CUL 技术 参数 UL/CUL Technical Data					
等 级 Use Group	B	C	D		
额定电压 Rated Voltage [V]	300	—	300		
额定电流 Rated Current [A]	8	—	8		
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	—				
耐电压 Withstanding Voltage	1600V/1Min				
IEC 技术参数 IEC Technical Data					
过电压类别 Overvoltage Category	III	III	II		
污染等级 Contamination Class	3	2	2		
额定电压 Rated Voltage [V]	160	160	250		
额定电流 Rated Current [A]	7	7	7		
额定冲击电压 Impulse withstand voltage [KV]	2.5	2.5	2.5		
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm ²]	—				
一般参数 Other Data					
间距 Pitch /极数 Poles [mm] / [P]	3.81/02-24				
工作温度 Operating temperature [°C]	-40~105				
焊锡温度 Soldering temperature	260°C/5S				
引针尺寸 Pin Dimensions [mm]	0.8*0.8				
PCB板孔径 PCB Hole Diameter [mm]	φ 1.4				
符合RoHS环保要求					

Poles	PART NO.	Dimension mm	
		A	B
2	G-DT38S02P-C000	8.41	3.81
3	G-DT38S03P-C000	12.22	7.62
4	G-DT38S04P-C000	16.03	11.43
5	G-DT38S05P-C000	19.84	15.24
6	G-DT38S06P-C000	23.65	19.05
...			
24	G-DT38S24P-C000	92.23	87.63

APPROVED:		DATE:	 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRY CO., LTD	
CHECKED:		DATE:		
DRAWN:		DATE:	绿色端子台 DT15EDGVC-3.81-XP 直针座 封口	
YKX		2024-5-22	PART. NO. G-DT38SXXP-C000	
			UNIT mm SCALE free	
			FILE NO. Ckmtw-DT381-0010 REV. A WJ00	



P.C.B. LAYOUT

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

2	Pin	Copper Alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES