






ROHS



PIN No.	Signal Name
1	Vbus
2	D-
3	D+
4	GND
5	StdA_SSRX-
6	StdA_SSRX+
7	GND_Drain
8	StdA_SSTX-
9	StdA_SSTX+
Shell	Shield

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTES:

1.MECHANICAL:

MATING: 35N MAX.

WITHDRAWAL: 10N MIN.

DURABILITY: 1500 CYCLES

2.ELECTRICAL:

CURRENT: 1.8A Maximum for pin1 and pin4,
and 0.25A for all the other pin.

VOLTAGE: 30 Vac (rms)

WITHSTANDING VOLTAGE: 100V AC

CONTACT RESISTANCE:

30 mΩ (Max) initial for pin1 and pin4.

50 mΩ (Max) initial for all other contacts.

Maximum change of +10mΩ after environmental stresses.
Measure at 20 mV (Max) open circuit at 100 mA.

DIELECTRIC WITHSTANDING VOLTAGE: 100V AC(RMS)

INSULATION RESISTANCE: 100MΩ MIN.

3.ENVIRONMENTAL

TEMPERATURE RANGE -25°C ~ +85°C

ITEM	PART NAME	Q'TY	Material
1	Molding	1	PBT(A-178),UL94V-0 BLUE,GOLD 30U"
2	SHELL	1	C2680R-H, 80u"MIN 可焊镍 盐雾48H
3	CONTACT1	4	C5191R-EH, GOLD 30U" 盐雾48H
4	CONTACT2	5	C2680R-H,GOLD 30U" 盐雾48H

CUSTOMER DRAWING

LAILIAN 深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO.,LTD

DRAWING	
CHECK	
APPROVAL	

TITLE	USB连接器4PIN-H15.0 (夹板)	REV.	A
-------	-----------------------	------	---

TOLERANCES ARE		
30-150	±0.35	ANGLE ±3°
10-30	±0.2	
5-10	±0.15	
0-5	±0.1	

PART NO.	LAIL-TYPE-A-4P-07Y-JB	UNITS	mm
DWG.NO.		Projection	