

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au Or Tin Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30–60 seconds



(260°C for 10 seconds)



Ordering Information

P X X X XX X X XX X XXXX

产品类别 P=材料	期望高度 A=1.27 B=1.27 C=1.5 D=2.0 E=3.0 F=3.8 G=5.1 H=12.7 I=5.4	特殊 A=单峰 B=2及峰 C=3 D=四峰 E=四峰	单峰N/A 1~40	产品标志 1=DP 2=NT 3=NT 4=ST 5=模纹	塑胶材料 1=BT 2=CP 3=PS 4=PA6 5=PA6T 9=PA9T	电镀厚度 00=常规 01=1 02=2 03=3 04=4 05=5 06=6 07=7 08=8 09=9 10=10	包卷力 1=常规 2=轻 3=中 4=重 5=叠卷
--------------	--	--	---------------	--	---	--	--



Dimension antitheses list								
ITEM	PA	PB	PW	L1	L2	L3	H	W
001	6,00	3,20	5,00	11,00			2,5	2,5
Alternate								

[illegible]