



客户确认	
日期	



PC Board Layout
Component Side Shown



- NOTES:
- MATERIAL :
- 1.HOUSING MATERIAL :PA 4 6 UL94V-0.
 - 2.CONTACT MATERIAL :PHOSPHOR BRONZE φ0.46mm.
 - 3.PLATING :GOLD PLATING OVER NICKEL.
- ELECTRICAL:
- 1.VOLTAGE RATING :125 VAC RMS.
 - 2.CURRENT RATING :1.5 AMP.
 - 3.CONTACT RESISTANCE :30 MILLIOHMS MAX.
 - 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC .
 - 5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.
- MECHANICAL:
- 1.DURRABILITY :750 CYCLES MIN.
 - 2.PCB RETENTION PRE-SOLDER :1 LB MIN.
- ENVIRONMENTAL:
- 1. STORAGE : -40℃~+85℃
 - 2. OPERATION : -25℃~+80℃

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

核准:	日期:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD				
业务:	日期:	品名规格: 网口插座 RJ45-8P/8C 全塑无筋 无灯 弯插 (PA46料)				
制图:	日期:	PART. NO.	R-RJ45R08P-AT04			
luli-Liu	2023-03-18	单位	mm	比例	/	☉
		图纸编号	Ckmtw-RJ45-0299	版本	A	RH00