






General Specification
Current Rating: 1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment
Standard Temperature: -20℃~+70℃
Industrial Temperature: -40℃~+85℃
Humidity: 20~70%
Contact Resistance: ≤30mΩ
Insulation Resistance: ≥500MΩ
Dielectric Strength: 500V AC/(50HZ)/Min
Mating And Unmating Force: 3~20N
Durability: 750 Cycles Min

Material Specification
Housing :Thermo-plastic, UL94V-0.
Contact :Alloy Copper
Shield :Alloy Copper

Please refer to the customer drawing when customer has specified



PCB LAYOUT
RECOMMENDED

网络插座外形图



温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

绘图:	日期:	2023.5.14
审核:	日期:	
批准:	日期:	
名称:	品名:	RJ45 无灯全塑
料号:	料号:	SP35TP-800000021B22 (RC02058)
型号:	型号:	RJ45
单位:	单位:	mm
比例:	比例:	1:1
纸张:	纸张:	A4