





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A2	ECN-P-2026041501	A2X5	产品材质及尺寸变更	2026.04.16	山楂
A3	/		系列图拆分	2026.08.04	山楂



PCB LAYOUT

- Specifications (规格):
- 1.Voltage rating (额定电压): DC 30V
 - 2.Current rating (额定电流): 0.5A AC/DC
 - 3.Withstanding voltage (耐压值): $\geq 500V$ AC/minute
 - 4.Insulation resistance (绝缘电阻): $\geq 100M\Omega$ Min
 - 5.Contact resistance (接触电阻): $\leq 30m\Omega$ Max
 - 6.Mating cycles (使用寿命): 5000 cycles Min
 - 7.Insertion and extraction force (插拔力): 3~20N



11	Shaft Sleeve		Brass	
10	Plastic 2	1	POM	White
9	Cover	1	POM	White
8	Plastic 1	1	PBT	Black
7	Terminal 7	1	Phosphor Bronze $\delta = 0.25mm$	Ag
6	Terminal 6	1	Phosphor Bronze $\delta = 0.25mm$	Ag
5	Terminal 5	1	Brass $\delta = 0.3mm$	Ag
4	Terminal 4	1	Brass $\delta = 0.3mm$	Ag
3	Terminal 3	1	Phosphor Bronze $\delta = 0.25mm$	Ag
2	Terminal 2	1	Phosphor Bronze $\delta = 0.25mm$	Ag
1	Terminal 1	1	Phosphor Bronze $\delta = 0.3mm$	Ag

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	山楂	VIEW:		MODEL TYPE:	3.5 PHONE JACK
CHECKED		UNIT:	mm/in	PART NO.:	PJ-3340-2
APPROVED		SIZE:	A4	DWG NO.:	