



XunPu

东莞市讯普电子科技有限公司

Dongguan Xunpu Electronic Technology Co., Ltd

承 认 书

SPECIFICATION FOR APPROVAL

客 户 名 称 Customer: _____

贵司料号CUSTOMER P/N: _____

FFC cable 1.0mm 4P, total length 100mm, co-directional, gold finger 4mm, reinforcing plate 8mm

敝司料号INTERIOR P/N: FFC-1.0-4-100-A-4-8

贵公司承认印 Approval signatures


料 号/Part No.	签 章/Signatures

Send us a copy of reference, thank you!

日期 Date:

拟制/Drawn	李明
审核/Check	李军
批准/Approved	向锐





Precautions

- The body image is for relationship comparison only, and everything is subject to the specifications of the data sheet.

Structure			
NO	Project	Specification	Remark
1	Insulating film	Print 20624	43um 60V 80C
2	Stiffeners	Blank film	43um
3	Conductor	Blue	225um PET
4	Conductor	Thickness	0.035 ±0.005
	plating	Width	0.3 ±0.03
		Electroplate	Tin Sn ≥40u"
		Electroplate	

Size			
Number of conductor	N	4	
Spacing	P	1.0	±0.05
Total spacing	Pt	3	±0.08
Overall width	W	5	±0.08
Edge width	M	1.0	±0.08
Overall length	L	100	±1.5
Mating thickness	T1	0.3	±0.05
Thickness of the	T2	0.12	±0.03
The inclination of the	A	—	≤0.3
Punching inclination	B	—	≤0.5
The length of the bare	S1/S2	4/4	±0.05
Length of stiffener	B1/B2	8/8	±1.5

Ancillary checklists			
NO	Project	Specification	Quantity
1			
2			
3			

- Shelf life: 12 months for gold plating; Tin plating for 6
- Storage environment: temperature 0°C-38°C; Humidity

Specifications and models:	FFC-1.0-4-100-A-4-8		
Customer part number:	Customer model:	date	
Version	What's Changed		
A/O	New production	2022/09/05	



XunPu 东莞市讯普电子科技有限公司

Name:	FFC flexible	Figure number:	XP2022090501	Drawing:	Li ming
Proportion:	1:1	Unit:	Millimetre(mm)	Audit:	Chen Jun
Vision:	◆	Page number:	Page 1 of 1	Approved:	Xiang Yu