




HOUSING:LCP 30% G/F UL 94V-0
COLOR:BLACK
CONTACT:BRASS C2680R-H,T=0.25mm
PEG: BRASS C2680R-H,T=0.30mm

CONTACT:1u",3u",5u",15u"GOLD PLATING
ON CONTACT AREA

100u" MIN.TIN PLATING ON SOLDERTAILS
40u" MIN.NICKEL UNDERPLATING OVER ALL

CURRENT RATING:1.5 AMPERE PER CONTACT
CONTACT RESISTANCE:30 MILLIOHMS MAX
INSULATION RESISTANCE:1000 MEGOHMS MIN
DIELECTRIC WITH STANDING VOLTAGE:500 VDC
OPERATING TEMPERATURE: -40°C ~ +85°C



SECTION:Y-Y

环保要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-SATA-01-22PSTG		版本 REV.	A
3	Peg	Brass C2680		Tin/Ni Plated				X. ±0.30	X.* ±3°	审核	LEO			品名 TITLE	SATA7+15P公座插板式SMT H0.9(半电气)		页次 SHEET	1/1
2	Terminal	Brass C2680		Gold/Tin Plated				X.X ±0.20	X.X* ±2°	CHECK	JOHN			客户料号 CUTM.NO.				
1	Housing	High Temp	Black	UL 94V-0				X.XX ±0.05	X.XX* ±0.5°	核准 APPROVAL				 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.				
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK						单位 UNITS	MM	比例 SCALE	1:1					
1		2		3		4		5		6		7		8		9		