





## 1. 产品尺寸图Product Dimension Drawing



## 2. 产品电器参数Product electrical parameters

|                                                      |                 |
|------------------------------------------------------|-----------------|
| 防护等级 (Ingress protection)                            | IP50            |
| 插拔测试 (Plugging and unplugging test)                  | <500次           |
| 产品耐温 (The product is temperature resistant)          | -20° C / +85° C |
| 盐雾腐蚀 (Salt Spray Corrosion)                          | >48 hr          |
| 额定电流Current rating                                   | 5A              |
| 额定电压 (Rated voltage)                                 | 250V            |
| 工作电压 (AC.V)<br>Operating voltage (AC.V)              | 250             |
| 耐电压 (AC.V)<br>Withstand voltage (AC.V)               | 1500            |
| 绝缘阻抗 (mΩ) DC500V<br>Insulation Resistance (mΩ)DC500V | 1500            |
| 绝缘电阻 (mΩ) DC1A<br>Insulation Resistance (mΩ)DC1A     | 5               |

### 3. 环境及表面处理产品特性Environmental and surface treatment product characteristics

|                          |                                |
|--------------------------|--------------------------------|
| 外壳材料 Housing material    | 锌合金镀镍Zinc alloy nickel plating |
| 绝缘体材料 Insulator material | 橡胶黑木Rubber black wood          |
| 触体材料 Contact material    | 黄铜镀金alum plating               |

|                                                                                                                                                                                                            |                                                                                     |                                                                                                   |                                                                                                                          |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|
| 1: 连接器组装生产所有公差通常为0.1mm,2: 插座直接拧入螺纹孔中, 螺纹 +0.05mm<br>1: All tolerances are usually 0.1mm for connector assembly production, 2: The socket is screwed directly into the threaded hole, the thread is +0.05mm |  | 东莞市通瑞电子科技有限公司<br>TongRuiJoin<br>Dongguan Tongrui Electronic Technology Co., Ltd<br>www.Cltfre.com | 单芯图纸Single-core drawings                                                                                                 |
|                                                                                                                                                                                                            |                                                                                     |                                                                                                   | 单位unit:mm    修改revise:A<br>视图view:  |
|                                                                                                                                                                                                            |                                                                                     | GX12弯针板接插座GX12<br>curved pin board socket                                                         | 型号Model<br>AD. GZ. GX12. 304. NJLV                                                                                       |