

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance:800MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass



Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)



Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds

(260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

J X XXX X XX X X X XXXX

产品类别 J= 筒式	间距	总Pin数	产品形态	电镀厚度	塑胶材料	塑胶颜色	包装方式	序列号
	1=1.27	016=16P	1=DIP	00=常规	1=PBT	1=黄色	1=管接	0001-9999
	2=2.0		2=RA	01=1u"	2=LCP	2=灰色	2=直插	
	3=2.54		3=SMT	02=2u"	3=PPS	3=白色	3=弯插	
	4=3.96		4=SH	03=3u"	4=PA46	4=黄色	4=接插	
	5=1.0		5=线插	04=4u"	5=PA6T	5=红色	5=盒装	
	6=0.8				9=PA9T	6=黄色		
	7=3.08					7=灰白色		
	A=1.27*2.54							

Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001		2.8		5.65	5.5
002					

				OPERATION		DRAW		SCALE		FIT		深圳市连盛精密连接器有限公司			
				X.X	±0.30			UNIT	mm						
				X.XX	±0.20	CHECK				SIZE	A4				
				X.XXX	±0.10					SHEET	1/1				
REV	DATE	MODIFICATION DESCRIPTION				CHANGE	DIM	TOL	APPROVE					PROJ.	TITLE:
A0	2012.03.28	NEW DRAWING												PART NO.	1030200144

深圳市连盛精密连接器有限公司

1030200144

2.0Box Npin H5.65 180°