



产品编号：[982660430](#)
Product Description：0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 76.00mm Cable Length, Tin (Sn) Plating, 40 Circuits
系列号：98266
状态：Active
Product Category：Flexible Printed Circuit (FPC) Flex Jumpers



文件和资源

图纸
[图纸 982660430_sd.pdf](#)

规格
[产品规格 PS-98266-001-001.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

多部分产品合规性声明

- Eu RoHS
- REACH SVHC
- Low-Halogen

多部分行业合规性文件

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

产品详情

常规

状态	活动
类别	Flexible Printed Circuit (FPC) Flex Jumpers
系列	98266
说明	0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 76.00mm Cable Length, Tin (Sn) Plating, 40 Circuits
个评论	Contacts on opposite sides, Type D
产品系列	FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
产品名称	Premo-Flex FFC Jumper
UPC	756054768846

电气

每触点最大电流	0.5A
电压 - 最大	60V AC

物理

电缆长度	76.00mm
回路数（已载入）	40
触点布局类型	D (opposite side)
材料 - 接合部位电镀	Tin
净重	1.018/g
包装形式	Bag
间距 - 插配接口	0.50mm
运行温度范围	-40° to +105° C
导线/电缆型号	Flat Flex Cable
线径规格（AWG）	不适用

可配插/可连接使用的产品

可配插部件

描述	产品编号
Easy-On FFC/FPC Connector, 0.50mm Pitch, V-Flip Series, Vertical, 4.05mm Height, 40 Circuits, Copper Alloy, Tin-Bismuth Plating	<u>5019514000</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Vertical, 3.90mm Height, 40 Circuits, Tin-Silver-Bismuth Plating	<u>0525594033</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Top Contact, 2.00mm Height, 40 Circuits, Tin-Silver-Bismuth Plating	<u>0541044033</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Bottom Contact, 2.00mm Height, 40 Circuits, Tin-Silver-Bismuth Plating	<u>0541324033</u>