







- 技术参数:
- 1. 做用温度: -25~+85℃;
 - 2. 额定负荷: DC 12V 50mA;
 - 3. 接触电阻: ≤50mΩ;
 - 4. 绝缘电阻: ≥100MΩ;
 - 5. 耐 压: AC250V (50Hz)/min;
 - 6. 动 作 力: 260±50g;
 - 7. 使用寿命: 5, 0000次;



Part NO.	H 高度
TC-S3603-4.3-260G-05	4.3
TC-S3603-4.5-260G-05	4.5
TC-S3603-5.0-260G-05	5.0
TC-S3603-5.5-260G-05	5.5
TC-S3603-6.0-260G-05	6.0
TC-S3603-6.5-260G-05	6.5
TC-S3603-7.0-260G-05	7.0
TC-S3603-8.0-260G-05	8.0

5	接触脚	1	黄铜	镀银	
4	基座	1	PPA	黑	
3	盖板	1	黄铜	铜锡	
2	簧片	1	不锈钢		
1	按钮	1	PPA	黑	
序号	名称	数量	材料	镀层/颜色	备件

			GENE RL TOL E RANCE	制 图 DRAWING		<div> 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD</div>			
			DIM TOL	审 核 CHECK					
			X. X ±0.30	批 准 APPROVAL					
			X. XX ±0.20	比 例 SCALE					
1	初版发行		X. XXX ±0.10	投 影 Projection		产品名称 TITLE	轻触开关 (SMT 3.6x7.3mm 4脚贴片+2脚插板)	版 本 REV.	A
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°			产品料号 PART NO.	TC-S3603-NH-260G-05	单 位 UNITS	mm
						材 料 MATERIAL		页 次 SHEET	1/1