



SCHEMATIC



SPECIFICATION

1. Rating : DC 30V 5A.
2. Contact resistance: $\leq 50\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
4. Withstanding voltage: 500VAC .
5. Insertion and extraction force: 3-30N.
6. life test: 5,000 cycles.
7. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
8. Sign" * " is importance dimension.

Tel: 0769-82310511-867

3	TERMINAL	PHOSPHOR COPPER	1	Ag-PLATED
2	PIN	BRASS	1	Ag-PLATED
1	HOUSING	PA66	1	BLACK
NO.	PART	NAME	QTY	FINISHING

TOLERANCE UNLESS SPECIFIED						
<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°					
		NO	DATE	REVISIONS		BY APPD
TITLE: DC JACK			UNIT : MM	ROHS	DWN	
MODEL: RT-C30-BA-09			SCALE: 1:1	COMPLIANT	CHK'D	
 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD		
				PRO.AGL:  		REV :A0