



东莞市讯普电子科技有限公司
Dongguan Xunpu Electronic Technology Co.,

承 认 书

SPECIFICATION FOR APPROVAL

客 户 名 称 Customer: _____

贵司料号CUSTOMER P/N: _____

FFC cable 1.0mm,5P,total length 100mm,reverse,gold finger 4mm,reinforcing plate 8mm

敝司料号INTERIOR P/N: _____ FFC-1.0-5-100-B-4-8

贵公司承认印 Approval signatures




料 号/Part No.	签 章/Signatures

Send us a copy of reference, thank you!

日期 Date:

拟制/Drawn	李晴
审核/Check	陈军
批准/Approved	陈钰





Precautions

1. The body image is for relationship comparison only, and everything is subject to the specifications of the data sheet.

Structure

NO.	Project	Specification		Remark
1	Insulating film	Print 20624	43um	60V 80C
		Blank film	43um	
2	Stiffeners	Blue	225um	PET
3	Conductor tinning	Thickness	0.035	±0.005
		Width	0.3	±0.03
4	Conductor plating	Electroplate	Tin Sn	≥40u"
		Electroplate		

Size

Number of conductor cores	N	5	
Spacing	P	1.0	±0.05
Total spacing	Pt	4	±0.08
Overall width	W	6	±0.08
Edge width	M	1.0	±0.08
Overall length	L	100	±1.5
Mating thickness	T1	0.3	±0.05
Thickness of the thread	T2	0.12	±0.03
The inclination of the line mouth	A		≤0.3
Punching inclination	B		≤0.5
The length of the bare copper at the wire port	S1/S2	4/4	±0.05
Length of stiffener	B1/B2	8/8	±1

Ancillary checklists

NO.	Project	Specification	Quantity
1			
2			
3			

1. Shelf life: 12 months for gold plating; Tin plating for 6 months.
2. Storage environment: temperature 0°C~38°C; Humidity 20%~70%RH.

Specifications and models:

FFC-1.0-5-100-B-4-8

Customer part number:

Customer model:



东莞市讯普电子科技有限公司

Version	Content of change	date	Name:	FFC flexible cable	Figure number:	XP2024080501	Drawing:	Li ming
A/O	New production	2022/09/05	Proportion:	FIT	Unit:	Millimetre(mm)	Audit:	Chen Jun
			Vision:		Page number:	Page 1 of 1	Approved:	Xiang Yu