



PCB LAYOUT

Notes:
Rated current:3.0A
Withstand Voltage:500V AC/DC
Contact Resistance:2mΩ Max
Insulation Resistance:1000MΩ Min
Operating Temperature:-40℃ TO +105℃
Contact Material:Brass
Plating:Gold Flash
Insulator Material: PA6T UL94V-0 BK

NO.	DATE	DESCRIPTION	APPROVAL	DRAWING:	GENERAL TOLERANCE	
1	24-06-11	初次发行	Jack	MAO ZI HAO		
2				CHECKED:	UNIT: MM PROJECTION	
3				YAO HUI SONG		
4				APPROVAL:	SCALE: N/A SHEET: 1/1	
5				HAN XIAO QIU		

东莞市文章济美电子有限公司		DESCRIPTION: PH2.54*2.5 2*NP PA6.0 PH6.9 PC3.0 90°	
		PART NO: 5001-040892-B	REC:1.0
SERIES :		ROHS	