





|      |           |          |                 |            |        |
|------|-----------|----------|-----------------|------------|--------|
|      | REVISIONS |          |                 |            |        |
| REV. | ECN NO.   | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0   | N/A       |          | INITIAL RELEASE | /          | /      |
| A1   | N/A       |          | 图面升级整理图面        | 2025.05.22 | 阿树     |



Specifications:

规格:





- 1.Voltage rating:250VAC/DC  
额定电压: 250V AC/DC
- 2.Current rating:3A(T) / 5A(C) AC/DC  
额定电流: 3A(T) / 5A(C) AC/DC
- 3.Withstanding voltage:500V AC/minute  
耐受电压: ≥500V AC/分钟
- 4.Temperature range: -55℃+105℃  
温度范围: -55℃+105℃
- 5.Insulation resistance:1000MΩMIN  
绝缘电阻: ≥1000MΩ
- 6.Contact resistance:30mΩMax  
接触电阻: ≥30mΩ
- Material:  
材料:
- 7.Rubber core:PBT UL94V-0  
胶芯: PBT UL94V-0
- 8.The iron shell:SPCC Nivkel Plating/Tin Plating/Gold Plating  
铁壳: SPCC,镀镍/镀锡/镀金
- B、成品不能有弯针, R角不一致等不良。

PART NO.:

X02 09 W I 7 W 5  
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series NO.  
②Row No.Pin No.XX-09;15;25;37  
③Welding Board Angle :W-Male  
④T: Traditional C: Car-pin  
⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U'  
⑥Color:B-BLACK W-White BL-Blue  
⑦1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7

| NUMBER OF POSITIONS | DIMENSION |        |        |        |
|---------------------|-----------|--------|--------|--------|
|                     | A±0.25    | B±0.13 | C±0.38 | D±0.13 |
| 9                   | 30.80     | 24.99  | 18.00  | 19.20  |
| 15                  | 39.20     | 33.32  | 26.50  | 27.50  |
| 25                  | 53.05     | 47.04  | 40.00  | 41.20  |
| 37                  | 69.40     | 63.50  | 56.60  | 57.70  |

| 铆合方式               | TYPE-1:铆合                                                                             | TYPE-2:前铆实心螺母                                                                                  | TYPE-7:后铆鱼叉                                                                           | TYPE-5:铆鱼叉锁螺丝                                                                         |                |
|--------------------|---------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|----------------|
| 图示                 |  |           |  |  |                |
| DESIGN             | 阿树                                                                                    | VIEW:<br> | MODEL TYPE:<br>D-SUB                                                                  |                                                                                       |                |
| CHECKED            |                                                                                       | UNIT: mm/in                                                                                    | PART NO.:<br>X0209WT7W5                                                               |                                                                                       |                |
| APPROVED           |                                                                                       | SIZE: A4                                                                                       | DWG NO.:<br>X-X0209WT7W5                                                              |                                                                                       |                |
| CISION CO.,LIMITED |                                                                                       |                                                                                                | SCALE<br>N/A                                                                          | PAGE<br>1/1                                                                           | REVISION<br>A1 |

|                        |               |
|------------------------|---------------|
| AuGLAR                 | $\pm 5^\circ$ |
| X.                     | $\pm 0.40$    |
| X.x                    | $\pm 0.30$    |
| X.xx                   | $\pm 0.20$    |
| X.xxx                  | $\pm 0.15$    |
| UNSPECIFIED TOLERANCES |               |

XKIB 星城 Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED