









RoHS Compliant








DETAIL:B
SCALE:2/1



DETAIL:C
SCALE:2/1

MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)		联晟欣连接器 (深圳) 有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24
X. ±0.25		CHECKED		DATE	
X.x ±0.20		APPROVED		DATE	
X.xx ±0.15		PART NO: LCK542BA0182A		REV: 04	SCALE: 1:1
ANGULAR ±3°		DRAWING NO: 102022802		SIZE: A4	UNIT: mm
		TITLE: 充电弹片 L3.27×W1.34×H5.86 Shielding Clip, SMT		SHEET: 1/1	

RoHS Compliant



▽
X direction - Force value
optimization improvement

↖
↙
↘
↗
Q(Spring Force-x direction)

- (1) MATERIAL:
1-1: STAINLESS STEEL THICKNE=0.10mm
- (2) FINISH:
2-1: 20u"min Au PLATING ON CONTACT AREA,
1u"min Au PLATING ON CONTACT AREA,
50u"min NICKEL UNDER PLATING OVER ALL.
2-2: DIMENSIONS OF PCB PAD STENCIL ARE FOR REFERENCE ONLY,
CUSTOMER CAN MODIFY IT BY THEIR OWN.
- (3) PRODUCT SPECIFICATIONS:
3-1: RATED CURRENT: 1.5A/MAX
3-2: VOLTAGE RATING: 5.0V/AC/DC/MAX
3-3: CONTACT RESISTANCE: 50mΩ/MAX
3-5: OPERATING TEMPERATURE: -40°C~85°C
3-6: NORMAL FORCE: 25gf+10/-5.
3-7: DURABILITY: 15,000 CYCLES,
- (4): SALT SPRAY: 48 HOURS(JUDGED BY OUTSIDE AREA)
- (5): PACKING SPECIFICATION: REEL&TARE
- (6): DIMENSIONS MARKED ,CPK >1.33
- (7): ALL DIMENSIONS MARKED MUST BE CONTROLLED BY QC;
- (8): COMPLIANT TO RoHS&LEAD FREE
- (9): PART NO.;

MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT	 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd				TITLE: 充电弹片L3.27×W1.34×H5.86 Shielding Clip,SMT
UNLESS OTHERWISE SPECIFIED,TOLERANCE:	DESIGN	Andy	DATE	2014.12.24	REV: 04
X. ±0.25	CHECKED		DATE		SCALE: 1:1
X.x ±0.20	APPROVED		DATE		UNIT: mm
X.xx ±0.15	PART NO: LCK542BA0182A				SIZE: A4
ANGULAR ±3°	DRAWING NO: 102022802				SHEET: 1/1