

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20m Ω Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au Or Tin Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30–60 seconds



(260°C for 10 seconds)



Ordering Information

P X X X XX X X XX X XXXX

产品类别	P=材料	颜色	A=1.27 B=2.0 C=2.5 D=3.6 E=5.0 A=1.27~2.54	厚度	B=1.5 C=2.0 D=2.5 E=3.6 A=四特	材质	1=单片 2=双片	单件尺寸	1~40P	产品形态	D=RA 2=CP 3=PMS 4=PP46 5=橡胶脚	塑胶材料	1=PBT 2=PC 3=PES 4=PA66 5=PBT	电镀厚度	00=常规 02=3" 03=3"	包装方式	1=背装 2=侧装 3=盒装 4=盘装 5=盒装
------	------	----	---	----	--	----	--------------	------	-------	------	--	------	---	------	-------------------------	------	--------------------------------------



Dimension antitheses list								
ITEM	PA	PB	PW	L1	L2	L3	H	W
001	6,00	3,20	5,00	11,00			2,5	2,5
Alternate								

[illegible]