








RoHS Compliant



RECOMMENDED PCB LAYOUT
TOP VIEW (TOL:±0.1)

NOTES:

- Material:
Insulation:Thermal Plastic? UL94V-0(Nature)
Pin:Phosphor Bronze/Tin-Plated
Tab:brass/Tin-Plated
- Current Rating:1A AC,DC
- Voltage Rating:125V AC,DC
- Temperature Rang:-25°~+85°
- Contact Resistance:20mΩ Max
- Insulation Resistance:100Ω Min
- Withstanding Voltage:500V AC/minute

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.			品名(ITEM NO)	1.0PH 3P 卧贴	
			料号(PART NO)	MLD-MX1.0-3PWT	
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次(REV): A/0	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	模号 (MODEL NO)		审核 (CHECKED)	邱敏
 		图号 (DWG NO)	MLD-2509031032	核准(APPROVED)	陈镇