

Features:

- 1.01~05 circuits available;
2. Material: PA66+30%GF 94V-0;
3. Contact: Phosphor Bronze;
4. Finished: Tin-plated or Gold-Flash;
5. Mates with H7920S12 Housing,
6. Coloe: Black/Natural/Red

Specification:

NO. of contacts	10 AWG	12 AWG	14 AWG	16 AWG
1	30 A	25 A	20 A	15 A
2	25 A	20 A	18 A	15 A
3	25 A	20 A	18 A	15 A
4	22 A	18 A	15 A	13 A
5	22 A	18 A	15 A	13 A

Current rating: 30A AC/DC.

Voltage rating: 600V AC(RMS) or 600V DC Max.

Contact resistance: 5mΩ Max.

Insulation resistance: 1000MΩ Min.

Withstanding voltage: 2500V AC/minute.

Ambient temperature rang: -35℃~90℃.

H7920S13-XX-XX-XX

SERIES NO:

PIN Q' PY:

01~05

Color:

CW-White

CB-Black



CR-Red

PLATING:








OT-Tin-plated

G1-G/F(ALL) 1U"



1 Pos.




2 to 5 Pos




Guide Key : Inside Color : White




PCB 2 to 5 Pos



PCB 1 Pos



Guide Key : Left Side, Color : Red



Guide Key : Right Side Color : Black

Dimensional Information(mm)

No. of Contacts	DIM A	DIM B
1		
2	17.22	7.92
3	25.14	15.84
4	33.06	23.76
5	40.98	31.68

REV

Description

DATE

GENERAL TOLERANCES
(unless specified)

UNITS

MM

DATE

2021-10-21

A

新版发行

2021-10-21

X.X±0.4

SCALE

1:1

DRAWING

Liu zhi guo

B

增加端子说明

2022-07-29

X.XX±0.25

REV

A

CHECKED BY

Li peng

PRODUCT NAME

7.92 mm vertical header

1

2

3

4

APPROVAL BY

OYSW

RART NUMBER

H7920S13-XX-XX-XX



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD