







技术指标:

1. 塑件表面应光洁, 无毛边, 无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ (含通电时的温度上升值).
3. 额定电压: 30V, AC/DC.
4. 接触电阻: 初期 $\leq 0.02\Omega$, 环境试验后 $\leq 0.04\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$ min.
6. 额定电流: 0.5A, AC/DC (使用 AWG#28, $0.038 \pm 0.02\text{mm}$).
7. 耐电压: AC 200V/1分钟.

材料:

1. 塑胶: LCP



型号	CKT	A	B	C	D
XY-HC0.8-2A41-GW	2	0.80	1.80	2.30	4.40
XY-HC0.8-3A41-GW	3	1.60	2.60	3.10	5.20
XY-HC0.8-4A41-GW	4	2.40	3.40	3.90	6.00
XY-HC0.8-5A41-GW	5	3.20	4.20	4.70	6.80
XY-HC0.8-6A41-GW	6	4.00	5.00	5.50	7.60
XY-HC0.8-7A41-GW	7	4.80	5.80	6.30	8.40
XY-HC0.8-8A41-GW	8	5.60	6.60	7.10	9.20
XY-HC0.8-9A41-GW	9	6.40	7.40	7.90	10.00
XY-HC0.8-10A41-GW	10	7.20	8.20	8.70	10.80
XY-HC0.8-11A41-GW	11	8.00	9.00	9.50	11.60
XY-HC0.8-12A41-GW	12	8.80	9.80	10.30	12.40
XY-HC0.8-13A41-GW	13	9.60	10.60	11.10	13.20
XY-HC0.8-14A41-GW	14	10.40	11.40	11.90	14.00
XY-HC0.8-15A41-GW	15	11.20	12.20	12.70	14.80
XY-HC0.8-16A41-GW	16	12.00	13.00	13.50	15.60
XY-HC0.8-17A41-GW	17	12.80	13.80	14.30	16.40
XY-HC0.8-18A41-GW	18	13.60	14.60	15.10	17.20
XY-HC0.8-19A41-GW	19	14.40	15.40	15.90	18.00
XY-HC0.8-20A41-GW	20	15.20	16.20	16.70	18.80
XY-HC0.8-21A41-GW	21	16.00	17.00	17.50	19.60
XY-HC0.8-22A41-GW	22	16.80	17.80	18.30	20.40
XY-HC0.8-23A41-GW	23	17.60	18.60	19.10	21.20
XY-HC0.8-24A41-GW	24	18.40	19.40	19.90	22.00
XY-HC0.8-25A41-GW	25	19.20	20.20	20.70	22.80

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
X.X±0.30	X.*±5°	APR. Alex	TITLE: 0.8 Pitch C型 WTB触头			
X.XX±0.25	X.X*±1°	CHK. Jack	DWG NO. XY-HC0.8-NA41-GW			
			PROJ. 		CUSTOMER DRAWING	
X.XXX±0.15		DRA. Can	SIZE A4	SCALE 1:1	SHEET 1 / 1	REV. A