








技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100M\Omega$ 。



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

Part No	CKT	A	B	C	D	E
BTB0522G-2*5PBL3	2X5	2.00	3.10	4.60	5.52	4.10
BTB0522G-2*6PBL3	2X6	2.50	3.60	5.10	6.02	4.60
BTB0522G-2*7PBL3	2X7	3.00	4.10	5.60	6.52	5.10
BTB0522G-2*8PBL3	2X8	3.50	4.60	6.10	7.02	5.60
BTB0522G-2*9PBL3	2X9	4.00	5.10	6.60	7.52	6.10
BTB0522G-2*10PBL3	2X10	4.50	5.60	7.10	8.02	6.60
BTB0522G-2*11PBL3	2X11	5.00	6.10	7.60	8.52	7.10
BTB0522G-2*12PBL3	2X12	5.50	6.60	8.10	9.02	7.60
BTB0522G-2*13PBL3	2X13	6.00	7.10	8.60	9.52	8.10
BTB0522G-2*14PBL3	2X14	6.50	7.60	9.10	10.02	8.60
BTB0522G-2*15PBL3	2X15	7.00	8.10	9.60	10.52	9.10
BTB0522G-2*16PBL3	2X16	7.50	8.60	10.10	11.02	9.60
BTB0522G-2*17PBL3	2X17	8.00	9.10	10.60	11.52	10.10
BTB0522G-2*18PBL3	2X18	8.50	9.60	11.10	12.02	10.60
BTB0522G-2*19PBL3	2X19	9.00	10.10	11.60	12.52	11.10
BTB0522G-2*20PBL3	2X20	9.50	10.60	12.10	13.02	11.60
BTB0522G-2*22PBL3	2X22	10.50	11.6	13.1	14.02	12.60
BTB0522G-2*25PBL3	2X25	12.00	13.1	14.6	15.52	14.10
BTB0522G-2*30PBL3	2X30	14.50	15.6	17.1	18.02	16.60
BTB0522G-2*35PBL3	2X35	17.00	18.1	19.6	20.52	19.10
BTB0522G-2*40PBL3	2X40	19.50	20.6	22.1	23.02	21.60

序号	品名	材质	TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
①	0.5 Pitch B型单槽 立式BTB公座胶芯	LCP UL94 V-0 颜色:米黄色	X.±0.50	±1°	PART NO. BTB0522G-2*NPBL3	TITLE: 0.5 Pitch B型单槽 立式BTB公座业务图(单高2.2)			
			X.X±0.20						
②	0.5 Pitch B型单槽 立式BTB公座端子	铜合金/表面镀锡/表面点镀金	X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG			
			UNITS	mm					
③	0.5 Pitch B型单槽 立式BTB公座焊片	铜合金/表面镀锡	MATERILA	— — —	CHED: Olvia	 SCALE SHEET			
			FINISH	— — —	APPD: Ava				
									N:A