






ROHS




SECTION A



PCB LAYOUT

- 1.Current Rating: 2A AC, DC
- 2.Voltage Rating: 100V AC, DC
- 3.Temperatuer Range: $-40^{\circ}\text{C}\sim+105^{\circ}$
- 4.Contact Resistance: $20\text{m}\Omega$ Max
- 5.Insulation Resistance: $1000\text{M}\Omega$ Min
- 6.Withstanding Voltang: 800V AC/minute
- 7.Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



COSTOMER DRAWING			 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
CHECK							
APPROVAL							
TOLERANCES ARE			TITLE		针座 PIN距2.0 2PIN卧贴 (PH系列)	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PHC2.0-2P-01-PH-WT	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			±3°	DWG. NO.		Projection	