

Rohs

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20m Ω Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au Or Tin Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T



Max. Processing Temp: 230°C for 30–60 seconds

(260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)

Ordering Information



产品类别	重量高度	挂装	单排N/A	颜色彩漆	塑封材料	电笔厚度	包装方式
P=特杆	A=1.27	1=特杆	1~40P	1-IDP	1=PBI	00=清漆	1=普通
	B=1.0	2=特杆		2-RA	2=PU	01=W	2=涂层
	C=2.54	3=特杆		3-SMT	3-PBS	02=2u"	3=涂层
	D=2.5	4=特杆		4-SH	4-PAD6	03=3u"	4=涂层
	A=1.27/2.54			5=镀锌钢	5-PAT		5=盒装
					9-PAGT		

Dimension antitheses list								
ITEM	PA	PB	PC	L1	L2	L3	H	W
001	6.00	4.30	3.00	13.80			2.5	2.5
Alternate								

深圳市连盛精密连接器有限公司											
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW			SCALE		FIT
				X.X	±0.30				UNIT	mm	
				X.XX	±0.20						
				X.XXX	±0.10						
				Angle	±3°						
A0	2012.07.02	NEW DRAWING			CHECK			SIZE	A4	SHEET	
								APPROVE			1/1
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL			PROJ.		TITLE:	2.54PH 1XNP 90度
										PART NO.	1010301724