


RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		




NOTES:
1.ELECTRICAL CHARACTERS:
1−1.RATING: DC 30V 0.5A;
1−2.CONTATCT RESISTANCE:≤30mΩ;
1−3.INSULATION RESISTANCE:≥100MΩ DC 500V;
1−4.WITHSTANDING VOLTAGE:AC 500V 1min;
1−5.LIFE:5,000 CYCLES;
2.MECHANICAL CHARACTERISTICS:
2−1.INSERTION&EXTRACTION FORCE:3~30N;
2−2.OPERATING TEMPERATURE:−30°C~+70°C;








PCB HOLES(TOP VIEW) t=1.6mm
GENERAL TOLERANCE:±0.05mm





SCHEMATIC

No.	PART NAME	TER'NO.	Q'TY	MATERIAL	REMARK
⑦	TERMINAL5#	5	1	Manganese steel t=0.2	SnSb PLATED
⑥	TERMINAL4#	4	1	BRASS t=0.35	CuSn PLATED
⑤	TERMINAL3#	3	1	BRASS t=0.35	CuSn PLATED
④	TERMINAL2#	2	1	Manganese steel t=0.2	SnSb PLATED
③	TERMINAL1#	1	1	BRASS t=0.25	CuSn PLATED
②	AXLE SLEEVE		1	BRASS	CuSn PLATED
①	HOUSING		1	NYLON	BLACK

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	MAT'L	TITLE: 耳机音频插座 PJ-3070 内径3.5MM 五脚直插 三级 带开关《环保车削》
.XX ±0.10	.XX° ± 0.5°	FINISH	APPD:
.XXX ± 0.05		Q'TY	CHKD:
			DR:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

DWG NO.: PJ-3070-3.5-20333

SCALE	SHEET	REV.
1/1	1/1	A1