2-1617534-6

ACTIVE

Half-Size Relays, Half-Size Relay Contact Arrangement 2 Form C, DPDT, 2 C/O, 12VDC Half-Size Relay Input Voltage



CII

TE Internal #: **2-1617534-6**
TE Internal Description: **HFW1201G15P=M39016/6-244P**
Mil-Spec: **M39016/6-244P**
Alias #: **HFW1201G15P**

Half-Size Relay Contact Arrangement: **2 Form C, DPDT, 2 C/O**
Half-Size Relay Input Voltage (VDC): **12**
Half-Size Relay Contact Current Rating (A): **2**
Half-Size Relay Coil Voltage Rating (VDC): **12**
Half-Size Relay Coil Resistance (Ω): **160**

Add to List | Similar Products |
Digital Datasheet

Compatible Parts & Tooling

THIS PART IS OUT OF STOCK

Similar Parts In Stock



Half-Size Relays, Half-Size Relay Contact Arrangement 2 Form...
TE Part #: 3-1617030-0
View Product



Half-Size Relays, Half-Size Relay Contact Arrangement 2 Form...
TE Part #: 1-1617036-0
View Product

View All Similar Parts

We are here to help!
Get in touch with our product experts.

CHAT WITH US
EMAIL US
CALL US

Documents | Features | Product Compliance

Please review product documents or contact us for the latest agency approval information.

Product Type Features

MOSFET Driver: **Without**
Product Type: **Relay**
Coil Latching: **Without**
Relay Type: **Military/Aerospace High Performance**
Enclosure Type: **Hermetically Sealed**

Configuration Features

Transistor Driver: **Without**

Electrical Characteristics

Coil Polarity Protection Diode: **Without**
Coil Power Measurement: **Milliwatts**
Coil Suppression Diode: **Without**
Half-Size Relay Input Voltage (VDC): **12**
Half-Size Relay Coil Voltage Rating (VDC): **12**
Half-Size Relay Coil Resistance (Ω): **160**
Half-Size Relay Coil Power Rating (DC) (mW): **900**
Half-Size Relay Contact Switching Voltage (Max): **28 VDC**
Shock: **100G's, 6ms**
Vibration: **30G's, 10 – 3000Hz**
Actuating System: **DC**
Coil Magnetic System: **Non-Polarized, Monostable**

Contact Features

Half-Size Relay Contact Arrangement: **2 Form C, DPDT, 2 C/O**
Half-Size Relay Contact Current Rating (A): **2**

Termination Features

Termination Type: **PC Pins**

Mechanical Attachment

Half-Size Relay Mounting Type: **Plain Case**

Usage Conditions

Operating Temperature Range (°C): **-65 – 125**

Compatible Parts

Filter By Specification



ASSOCIATED
JMGST-5MW
TO-5/.100 Grid Relays, 2 Form C, DPDT, 2 C/O, 5VDC TO-5/.100...
From: $45.090
In-Stock
VIEW PRODUCT

Products with Similar Specs

View All Similar Products

THIS PRODUCT	TOP RESULTS		
HALF-SIZE RELAYS	HALF-SIZE RELAYS	HALF-SIZE RELAYS	HALF-SIZE RELAYS
2-1617534-6	1-1617028-0	1-1617028-2	3-1617030-0
Half-Size Relays, Half-Size Relay Contact Arrangement 2 Form C...	Half-Size Relays, Half-Size Relay Contact Arrangement 2 Form C...	Half-Size Relays, Half-Size Relay Contact Arrangement 2 Form C...	Half-Size Relays, Half-Size Relay Contact Arrangement 2 Form C...
			
Non-Stocked	Non-Stocked	Non-Stocked	From $71.730 In-Stock
Half-Size Relay Contact Arrangement: **2 Form C, DPDT, 2 C/O** Half-Size Relay Input Voltage: **12 VDC** Half-Size Relay Contact Current Rating: **2 A** Half-Size Relay Coil Voltage Rating ...	Half-Size Relay Contact Arrangement: **2 Form C, DPDT, 2 C/O** Half-Size Relay Input Voltage: **12 VDC** Half-Size Relay Contact Current Rating: **2 A** Half-Size Relay Coil Voltage Rating ...	Half-Size Relay Contact Arrangement: **2 Form C, DPDT, 2 C/O** Half-Size Relay Input Voltage: **12 VDC** Half-Size Relay Contact Current Rating: **2 A** Half-Size Relay Coil Voltage Rating ...	Half-Size Relay Contact Arrangement: **2 Form C, DPDT, 2 C/O** Half-Size Relay Input Voltage: **12 VDC** Half-Size Relay Contact Current Rating: **2 A** Half-Size Relay Coil Voltage Rating ...

Customers Also Bought



TE Part #: **KUP-14D45-110**
Potter & Brumfield KUP, Power Relays, Industrial...
$66.240 per unit
Inventory: 139
Add To Cart



TE Part #: **WD2759-003**
Kilovac WD, Protective Relays, Protective Relay...
$1,140.360 per unit
Inventory: 3
Add To Cart



TE Part #: **CB5443-000**
Raychem XFFR, Heat Shrink Tubing, Black, Single Wall...
View Product



TE Part #: **1617147-2**
TO-5/.100 Grid Relays, 2 Form C, DPDT, 2 C/O...
View Product