









DETAIL A
SCALE 20:1





LOC		DIST		REVISIONS						
GE		00		REV	LYR	DESCRIPTION	DATE	DWN	APVD	
				D		REVISED PER EC OK40-0405-02	17APR2002	AH	TW	
				D1		REVISED PER EC OK40-0248-03	02SEP2003	AH	TW	
				E		REVISED PER OK40-0074-04	23MAR2004	AG	TW	
				F		REVISED PER ECR 05-003800	17NOV2005	DLD	JLT	

1 MATERIAL: 0.30 THICK COPPER ALLOY, PREPLATED WITH 0.0008 MINIMUM THICK MATTE TIN (ELV COMPLIANT).



4. QUALIFICATION OF THE CRIMP APPLICATION TOOLING SHALL BE CONTROLLED BY THE REQUIREMENTS ESTABLISHED UNDER USCAR 21.

5. LOOSE END SPLICING TO BE USED.



3	1-1326031-1 REELED FOR AMP APPLICATORS							12 AWG	1-1326031-2
	1.35	6.8	4.30	5.89	4.7	2.7	5.25	12 AWG	1-1326031-1
3	1326031-5 REELED FOR AMP APPLICATORS							14 AWG	1-1326031-1
	1326031-4 REELED FOR AMP APPLICATORS							16 AWG	1326031-9
	1326031-3 REELED FOR AMP APPLICATORS							18 AWG	1326031-8
	1326031-2 REELED FOR AMP APPLICATORS							20 AWG	1326031-7
2	1326031-1 REELED FOR AMP APPLICATORS							22 AWG	1326031-6
	1.35	6.5	4.30	5.62	3.9	1.70	3.88	14 AWG	1326031-5
	1.10	5.6	3.80	4.54	3.9	1.70	3.88	16 AWG	1326031-4
	1.10	5.6	3.80	4.54	3.3	1.30	2.76	18 AWG	1326031-3
	0.90	5.0	3.40	4.11	3.3	1.30	2.76	20 AWG	1326031-2
2	0.90	5.0	3.40	4.11	2.5	0.90	2.11	22 AWG	1326031-1
	REELING	N	L	ØK	J	H	ØF	E	WIRE SIZE

THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE AND THE CUSTOMER SHALL BE RESPONSIBLE FOR VERIFYING THE DIMENSIONS OF THE PARTS BEFORE USE. IF A CHANGE IS REQUIRED, THE CUSTOMER SHALL BE CONTACTED FOR THE LATEST REVISION.		DWN D. STRAUSSER 28APR99		Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK D. BROWN 28APR99		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.3 1 PLC ±0.10 2 PLC ±.1 3 PLC ±.1 4 PLC ±.1 ANGLES ±.5° FINISH		APVD D. BROWN 28APR99		PRODUCT SPEC SAE/USCAR-2 8/97	
MATERIAL		APPLICATION SPEC 114-13013		SIZE A	
CUSTOMER DRAWING		WEIGHT -		CAGE CODE 00779	
SCALE 10:1		DRAWING NO 114-13013		SHEET 1 OF 1	
REV F		CUSTOMER DRAWING		REV F	