
Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN	James		9/26



NOTES:

1. ELECTRICAL:
   - 1.1. VOLTAGE RATING:DCV 300V 10MS
   - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
   - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
   - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
   - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
   - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPITION	QTY.
③	套管	OD:3.5 *15mm 黑色热缩套管	2
③	接头	SMA直公头，镀金,接RG316线	1
②	接头	SMA弯公头，镀金,接RG316线	1
①	同轴线	RG316 棕色同轴线，外被:FEP ,OD:2.5MM	AS

深圳市金航标电子有限公司

ALL DIMENSION ARE IN MM		DATE	
	DRAWN James	2026-08-14	TITLE: KH-SMAJ-SMAJW-RG316-200
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING	CHKD. Frank	2026-08-14	
	APPD. Scott	2026-08-14	SIZE B / DWG Number. / REV A
PROJECTION	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1° ±0.3 ±0.25 ±0.150		SCALE:Free / TYPE / SHEET 1 OF 1

CUSTOMER P/N: