



Specifications:
规格：
Voltage rating:150V AC/DC
额定电压：150V AC/DC
Current rating:1A AC/DC
额定电流：1A AC/DC
Withstanding voltage:500V AC/minute
耐受电压：500V AC/分钟
Temperature range:-25℃-+85℃
温度范围：-25℃-+85℃
Insulation resistance:≥500MΩ min
绝缘电阻：≥500MΩ Min
Contact resistance:≤30mΩ Max
接触电阻：≤30mΩ Max

X9812 W V S - 2x06 - 6T V01
① ② ③ ④ ⑤ ⑥ ⑦

1.Series No
2.Category:W-Wafer
3.Welding Board Angle:V-Stright 180°
4.Welding Way:S-SMT
5.Row No.Pin No:XX-2x05~2x25P
6.Material:6T-PA6T UL 94V-0 Natural
CAP:PA6T UL 94V-0 Natural
7.Plating:V01-Gold Flash





P.C.B LAYOUT

Poles	Dimensions(mm)	
	A	B
2x02	1.25	8.75
2x05	5.00	12.50
2x06	6.25	13.75
2x07	7.50	15.00
2x10	11.25	18.75
2x12	13.75	21.25
2x15	17.50	25.00
2x20	23.75	31.25

X9812WVS-2x06-6TV01	PA6T	Brass	X9812H
PART N0	Material	Material(Pin)	Suitable XKB Housing

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS

UNSPECIFIED TOLERANCES	
ANGLAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN		VIEW:	PART NO.: X9812WVS-2x06-6TV01
CHKD		UNIT: mm/in	DWG NO.: X-X9812WVS-2x06-6TV01
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0